

# Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 120/24 V 60 Hz, NEMA 1

8903LXG60V89F4T

Price\*: 1,544.00 USD

! Discontinued

## Main

|                           |                                      |
|---------------------------|--------------------------------------|
| Product Or Component Type | Mechanically Held Lighting Contactor |
| Range Of Product          | 8903LX                               |
| Control Circuit           | Control circuit transformer          |

## Complementary

|                        |   |
|------------------------|---|
| Control Voltage        | 24 V AC 60 Hz secondary circuit<br>120 V AC 60 Hz primary circuit |
| Inrush Power In Va     | 180 VA 60 Hz<br>170 VA 50/60 Hz                                   |
| Current Rating         | 20 A tungsten<br>30 A fluorescent                                 |
| Number Of Poles        | 6P 6 NO   |
| Control Unit           | No control units  |
| Pilot Light            | No indicator  |
| Control Circuit Fusing | 2 fuses primary circuit   |
| Other Options          | None  |
| Electrical Connection  | Screw-clamp terminals   |
| Height                 | 11.89 in (302 mm)   |
| Depth                  | 7.44 in (189 mm)  |
| Width                  | 11.89 in (302 mm)   |

## Environment

|                        |                                    |
|------------------------|------------------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel surface |
| Product Certifications | UL Listed<br>CSA                   |

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

## Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                         |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1                       |
| Package 1 Weight             | 57.28 lb(US) (25.98 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

### California Proposition 65

WARNING: This product can expose you to chemicals including: Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

---