

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 8 P, 8 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 1

8903LXG80V04C6

Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	277 V AC 60 Hz
Inrush Power In Va	180 VA 60 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	8P 8 NO
Control Unit	Selector switch ON-OFF)
Pilot Light	No indicator
Other Options	None
Electrical Connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21322-8903 LX (NOT L)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	5.60 lb(US) (2.54 kg)
------------------	-----------------------

Contractual warranty

Warranty	18 months
----------	-----------