

Product data sheet


Characteristics

8903LXG80V04R6Y217

8903LX mechanically held lighting contactor, 8 P, 8 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 1



Price** : 1,650.00 USD



8903LXG80V04R6Y217 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	277 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 25 VA 50/60 Hz
Current Rating	20 A tungsten
Number of Poles	8P 8 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.8 in (198 mm)

Environment

Enclosure Type	Painted sheet steel NEMA 1 and with surface Mounting;
Product certifications	CSA UL listed

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Nbr. of units in pkg.	1

Package weight(Lbs)	44.050000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
