



Price** : 1,880.00 USD



8903LXG80V80CF4T has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Control circuit	Control circuit transformer
Device short name	LX
Enclosure type	Enclosure standard environment indoor
Product or component type	Mechanically Held Lighting Contactor

Complementary

[In] rated current	30 A
Auxiliary contacts type	Field convertible
Contacts material	AgCdO
Contact operation	Double-break
Contacts type and composition	8 NO
Control type	Selector switch HAND-OFF-AUTO
Depth	7.44 in
Device mounting	Surface
Electrical connection	Screw terminal
Height	11.88 in
Number of poles	8
Permissible voltage	<= 600 V AC
Primary voltage	240 V AC 60 Hz
Product destination	Motor control centre Lighting panel board
Secondary voltage	120 V AC 60 Hz
Width	11.88 in

Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E78427 CCN NRNT

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	57.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------