

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 8 P, 8 NO, 30 A, 600 V, 480/120 V 60 Hz, NEMA 1

8903LXG80V81FF4G101K141R6T

Price*: 3,945.00 USD

Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Inrush Power In Va	180 VA 60 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	8P 8 NO
Control Unit	No control units
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	2P relay (1 NO + 1 NC) 7-day time clock (with day omission)
Electrical Connection	Screw-clamp terminals
Height	22.01 in (559 mm)
Depth	7.13 in (181 mm)
Width	15.98 in (406 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface photoelectric receptacle with cell
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months