



Price* : 2,285.00 USD



8903LXG80V81FF4T11 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	8P 8 NO
Control Unit	No control units
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Electrical connection	Screw-clamp terminals

Environment

Enclosure Type	Painted sheet steel NEMA 1 and with surface Mounting;
Product certifications	CSA UL listed

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	57.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
