

# 8903LXG80V85FF4T

8903LX mechanically held lighting contactor, 8 P, 8 NO, 30 A, 600 V, 277/120 V 60 Hz, NEMA 1



Price\*\* : 1,985.00 USD



8903LXG80V85FF4T has not been replaced. Please contact your customer care center for more information.

## Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Control circuit transformer

## Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 277 V AC 60 Hz primary circuit
Inrush power in VA	180 VA 60 Hz 25 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	8P 8 NO
Control Unit	No control units
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	None
Electrical connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

## Environment

Enclosure Type	Painted sheet steel NEMA 1 and with surface Mounting;
Product certifications	CSA UL listed

## Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	57.5
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------