

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 4 P, 4 NO, 30 A, 600 V, 110/120 V 50/60 Hz coil, open

8903LXO40V02R62

Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush Power In Va	150 VA 60 Hz 150 VA 50 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	4P 4 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	3-wire long-distance control interface
Electrical Connection	Screw-clamp terminals
Height	8.82 in (224 mm)
Depth	3.27 in (83 mm)
Width	2.87 in (73 mm)

Environment

Enclosure Type	Not rated (open device)
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21322-8903 LX (NOT L)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	5.20 lb(US) (2.359 kg)

Contractual warranty

Warranty	18 months
----------	-----------