





Contactor, Type L, multipole lighting, mechanically held, 30A, 10 pole, 600 V, 24 VAC 60 Hz coil, NEMA 4/4X

8903LXW1000V01

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

## Complementary

Control Voltage	24 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	10P 10 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Other Options	None	
Electrical Connection	Screw-clamp terminals	
Height	16.18 in (411 mm)	
Depth	7.87 in (200 mm)	
Width	8.11 in (206 mm)	

## **Environment**

Enclosure Type	NEMA 4/4X brushed stainless steel surface
Product Certifications	UL Listed CSA

# Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	16.18 in (41.1 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	65.87 lb(US) (29.88 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>Ø</b>	Toxic Heavy Metal Free
<b>Ø</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free
<b>②</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov