


Price* : 3,522.00 USD



8903LXW20V81CC33FF4R6T has not been replaced.
Please contact your customer care center for more information.

Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	2P 2 NO
Control Unit	Key-operated selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Screw-clamp terminals

Environment

Enclosure Type	Brushed stainless steel NEMA 4/4X and with surface Mounting;
Product certifications	CSA UL listed

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	48.16000000000004
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------