# Product data sheet

Specifications



# Contactor, Type L, multipole lighting, mechanically held, 30A, 8 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 4/4X

8903LXW80V02CR6

Provide the discontinued on: Apr 30, 2024

# Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Mechanically Held Lighting Contactor	
Range Of Product	8903LX	
Control Circuit	Separate control circuit	
Complementary	/	
Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	8P 8 NO	
Control Unit		

Control Unit	Selector switch HAND-OFF-AUTO)	
Pilot Light	No indicator	
Other Options	2P relay (1 NO + 1 NC)	
Electrical Connection	Screw-clamp terminals	
Height	14.69 in (373 mm)	
Depth	7.80 in (198 mm)	
Width	12.64 in (321 mm)	

#### Environment

Enclosure Type	NEMA 4/4X brushed stainless steel surface
Product Certifications	UL Listed CSA

### Ordering and shipping details

Category	21322 - 8903 LX (NOT L)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	МХ	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.69 in (37.3 cm)
Package 1 Width	12.64 in (32.1 cm)
Package 1 Length	7.80 in (19.8 cm)
Package 1 Weight	41.96 lb(US) (19.033 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov