

8903PBM10V38

panelboard lighting contactor, 30 AMP, 2 pole,
panel mount, 120/208V 60Hz coil



8903PBM10V38 has not been replaced. Please contact your customer care center for more information.

Main

| | |
|-----------------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type | PB |
| Control Circuit | Common control circuit |

Complementary

| | |
|-------------------------------|--|
| Control Circuit Voltage | 120 V AC at 60 Hz |
| [In] rated current | 30 A |
| Number of Poles | 2P |
| AWG gauge | AWG 1/0 (aluminium/copper) , power wire AWG 18...AWG 10 (copper) , control wire |
| System Voltage | 600 V AC |
| Auxiliary contact composition | Without |
| Mounting support | Panel |
| Electrical connection | Lugs |
| Height | 11.73 in (298 mm) |
| Depth | 3.86 in (98 mm) |
| Width | 7.52 in (191 mm) |

Environment

| | |
|------------------------|------------------|
| Product certifications | CSA UL listed |
|------------------------|------------------|

Ordering and shipping details

| | |
|-----------------------|-----------------------|
| Category | 21323 - 8903 PB |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 8.0000000000000002E-2 |
| Returnability | N |
| Country of origin | MX |