

# Product data sheet

Specifications

SQUARE D



panelboard lighting cont, 30 AMP,  
3 pole, bus mount, 240/277V 60Hz  
coil, repair

8903PBM11BV39R

Discontinued

## Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

## Complementary

Control Circuit Voltage	240/277 V AC 60 Hz
Line Rated Current	30 A
Number Of Poles	3P
Awg Gauge	AWG 1/0 aluminium/copper)power AWG 18...AWG 10 copper)control
Maximum Overall Voltage	600 V AC
Auxiliary Contact Composition	Without
Mounting Support	busbar
Electrical Connection	Busbar connection
Height	8.31 in (211 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

## Environment

Product Certifications	UL Listed CSA
------------------------	------------------

## Ordering and shipping details

Category	21323-8903 PB
Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications