

Product data sheet

Specifications

SQUARE D



panelboard lighting contactor, 75 AMP, 2 pole, bus mount, 120V 60Hz coil

8903PBN10BV02

⚠ Discontinued on: Oct 14, 2020

⚠ Discontinued

Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Line Rated Current	75 A
Number Of Poles	2P
Awg Gauge	AWG 1/0 aluminium/copper)power AWG 18...AWG 10 copper)control
Maximum Overall Voltage	600 V AC
Auxiliary Contact Composition	Without
Mounting Support	busbar
Electrical Connection	Busbar connection
Height	8.31 in (211 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

Environment

Product Certifications	UL Listed CSA
------------------------	------------------

Ordering and shipping details

Category	21323-8903 PB
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Under investigation
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov