

Product data sheet

Specifications

SQUARE D



panelboard lighting cont, 75 AMP,
3 pole, panel mount, 120/208V
60Hz coil

8903PBN11V38X11

Discontinued

Main

| | |
|-----------------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type | PB |
| Control Circuit | Common control circuit |

Complementary

| | |
|-------------------------------|--|
| Control Circuit Voltage | 120 V AC 60 Hz |
| Line Rated Current | 75 A |
| Number Of Poles | 3P |
| Awg Gauge | AWG 1/0 aluminium/copper)power AWG 18...AWG 10 copper)control |
| Maximum Overall Voltage | 600 V AC |
| Auxiliary Contact Composition | 1 NO + 1 NC |
| Mounting Support | panel |
| Electrical Connection | Lugs |
| Height | 11.73 in (298 mm) |
| Depth | 3.86 in (98 mm) |
| Width | 7.52 in (191 mm) |

Environment

| | |
|------------------------|------------------|
| Product Certifications | UL Listed CSA |
|------------------------|------------------|

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | 21323-8903 PB |
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | MX |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications