

Product data sheet

Characteristics

8903PBV10BV02

panelboard lighting contactor, 200 AMP, 2 pole,
bus mount, 120V 60Hz coil

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 4,941.00 USD



Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

Complementary

Control Circuit Voltage	110 V AC at 50 Hz 120 V AC at 60 Hz
[In] rated current	200 A
Number of Poles	2P
AWG gauge	AWG 18...AWG 10 (copper) , control wire 350 kcmil (aluminium/copper) , power wire
System Voltage	600 V AC
Auxiliary contact composition	Without
Mounting support	Busbar
Electrical connection	Busbar connection
Height	9.49 in (241 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

Environment


Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21323 - 8903 PB
Discount Schedule	CP1

GTIN	00785901582724
Nbr. of units in pkg.	1
Package weight(Lbs)	7
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------