


# 8903PBW10BV38

panelboard lighting contactor, 225 AMP, 2 pole,  
bus mount, 120/208V 60Hz coil



8903PBW10BV38 has not been replaced. Please contact your customer care center for more information.

## Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

## Complementary

Control Circuit Voltage	120 V AC at 60 Hz
[In] rated current	225 A
Number of Poles	2P
AWG gauge	AWG 18...AWG 10 (copper) , control wire 350 kcmil (aluminium/copper) , power wire
System Voltage	600 V AC
Auxiliary contact composition	Without
Mounting support	Busbar
Electrical connection	Busbar connection
Height	9.49 in (241 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

## Environment

Product certifications	CSA UL listed
------------------------	------------------

## Ordering and shipping details

Category	21323 - 8903 PB
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	8.0000000000000002E-2
Returnability	N
Country of origin	MX