


Product data sheet

Characteristics

8903PBW11BV38X22

panelboard lighting cont, 225 AMP, 3 pole, bus mount, 120/208V 60Hz coil



8903PBW11BV38X22 has not been replaced. Please contact your customer care center for more information.

Main

Product	Mechanically Held Lighting Contactor
Type	PB
Control Circuit	Common control circuit

Complementary

Control Circuit Voltage	120 V AC at 60 Hz
[In] rated current	225 A
Number of Poles	3P
AWG gauge	AWG 18...AWG 10 (copper) , control wire 350 kcmil (aluminium/copper) , power wire
System Voltage	600 V AC
Auxiliary contact composition	2 NO + 2 NC
Mounting support	Busbar
Electrical connection	Busbar connection
Height	9.49 in (241 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

Environment

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21323 - 8903 PB
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N
Country of origin	MX