

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 912.00 USD



### Main

Product	Mechanically Held Lighting Contactor
Type	S

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	2P
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs

### Environment

Enclosure Type	NEMA 12 painted sheet steel surface and none
Product certifications	CSA UL listed

### Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	17.859999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Contractual warranty

Warranty period	18 months
-----------------	-----------