

Product data sheet

Characteristics

8903SMA11V02

lighting contactor, mechanically held, 30 A, 3 pole,
NEMA 12, 120/110V 60/50Hz

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 953.00 USD



Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs

Environment

Enclosure Type	NEMA 12 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	17.859999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------