

# Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 3 pole, NEMA 12, 277V 60Hz

8903SMA11V04

Price\*: 953.00 USD

! Discontinued

## Main

Product	Mechanically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	277 V AC 60 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

## Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

## Ordering and shipping details

Category	21324-8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications