

# Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,  
30 A, 2 pole, NEMA 12, 480-120V  
60Hz

8903SMA1V81CFF4P1T

⚠ Discontinued on: Aug 17, 2021

⚠ Discontinued

Price\*: 2,015.00 USD

## Main

Product	Electrically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	2P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	None
Electrical Connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

## Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications