

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 3 pole, NEMA 12, 120/110V
60/50Hz

8903SMA2V02F

Discontinued on: Aug 17, 2021

Discontinued

Price*: 1,002.00 USD

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	1 fuse
Other Options	None
Electrical Connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications