

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 3 pole, NEMA 12, 240/220V
60/50Hz

8903SMA2V03C

! Discontinued on: Aug 17, 2021

! Discontinued

Price*: 1,025.00 USD

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications