

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 4 pole, NEMA 12, 120/110V
60/50Hz

8903SMA3V02CNX20

! Discontinued on: Aug 17, 2021

! Discontinued

Price*: 1,565.00 USD

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number Of Poles	4P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Without pilot light
Auxiliary Contacts	2 NO
Other Options	Solid neutral terminal block
Electrical Connection	Lugs
Height	15.98 in (406 mm)
Depth	7.87 in (200 mm)
Width	14.88 in (378 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.