

# Product data sheet


## Characteristics

# 8903SMA3V02R174

lighting contactor, electrically held, 30 A, 4 pole,  
NEMA 12, 120/110V 60/50Hz



Price\* : 1,529.00 USD



8903SMA3V02R174 has not been replaced. Please contact your customer care center for more information.

### Main

Product	Electrically Held Lighting Contactor
Type	S

### Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	4P
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

### Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface and none
Product certifications	CSA UL listed

### Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	50
Returnability	N

Offer Sustainability

---

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---