


8903SMA82V03

combo lighting, electrically held, 3P, 30A, 240V
breaker, NEMA 12, 240V 60Hz



Price* : 1,742.00 USD



8903SMA82V03 has not been replaced. Please contact your customer care center for more information.

Main

Product	Combination electrically held lighting contactor
Type	S

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Disconnecter device type	Thermal magnetic circuit breaker 30 A at 240 V
Electrical connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface and none
Product certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	28.949999999999999

Returnability	N
---------------	---

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
