

Product data sheet

Specifications

SQUARE D



combo lighting, electrically held, 3P, 30A, 240V breaker, NEMA 12, 208V 60Hz

8903SMA82V08CF4G10

Discontinued

Main

Product	Combination electrically held lighting contactor
Type	S

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses
Disconnecter Device Type	Thermal magnetic circuit breaker, 30 A 240 V
Electrical Connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface photoelectric receptacle without cell
Product Certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21325-8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications