

Product data sheet

Specifications

SQUARE D



combo lighting, mechanically held,
3P, 30A, 240V breaker, NEMA 12,
120V 60Hz

8903SMA92V02

! Discontinued

Main

Product	Combination mechanically held lighting contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number Of Poles	3P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Disconnecter Device Type	Thermal magnetic circuit breaker, 30 A 240 V
Electrical Connection	Lugs
Height	12.76 in (324 mm)
Depth	8.54 in (217 mm)
Width	6.38 in (162 mm)

Environment

Enclosure Type	NEMA 12/3R painted sheet steel surface none
Product Certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21324-8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.