



Price** : 2,412.00 USD



8903SMC61V04G101 has not been replaced. Please contact your customer care center for more information.

Main

Type	Night-Master
------	--------------

Complementary

Control Circuit Voltage	277 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Auxiliary Contacts	Without
Disconnecter device type	Fusible disconnect switch, Type R Fuse, 30 A at 600 V
Electrical connection	Lugs
Height	23.5 in (597 mm)
Depth	10.51 in (267 mm)
Width	15 in (381 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel surface and photoelectric receptacle with cell
Product certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21326 - 8903 S*C
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	105
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
------------------------	-----------------------------

Will be compliant on 3Q2014

REACH

Reference not containing SVHC above the threshold
Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months
