



Price* : 2,732.00 USD



8903SMC61V81A12F4T has not been replaced. Please contact your customer care center for more information.

Main

Type	Night-Master
------	--------------

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Line Rated Current	30 A
Number of Poles	3P
Control Units	Push-button (ON-OFF)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Disconnecter device type	Fusible disconnect switch, Type R Fuse, 30 A at 600 V
Electrical connection	Lugs
Height	23.5 in (597 mm)
Depth	10.51 in (267 mm)
Width	15 in (381 mm)

Environment

Enclosure Type	NEMA 3R painted sheet steel surface and none
Product certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21326 - 8903 S*C
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	105

Returnability	N
---------------	---

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
