

# Product data sheet

Specifications

SQUARE D



NIGHT-MASTER, combo lighting contactor, 30 A, 3P, breaker, NEMA 3R, 240V 60Hz

8903SMC81V03G101

Price\*: 2,874.00 USD

! Discontinued

## Main

Type	Night-Master
------	--------------

## Complementary

Control Circuit Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Current Rating	30 A
Number Of Poles	3P
Auxiliary Contacts	Without
Disconnecter Device Type	Thermal magnetic circuit breaker, 30 A 600 V
Electrical Connection	Lugs
Height	23.50 in (597 mm)
Depth	10.51 in (267 mm)
Width	15.00 in (381 mm)

## Environment

Enclosure Type	NEMA 3R painted sheet steel surface photoelectric receptacle with cell
Product Certifications	UL listed file E16151 CCN NRNT

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	5.00 lb(US) (2.268 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications