

Product data sheet

Characteristics

8903SMG11V02CP22

lighting contactor, mechanically held, 30 A, 3 pole,
NEMA 1, 120/110V 60/50Hz



Price** : 1,548.00 USD



8903SMG11V02CP22 has not been replaced. Please contact your customer care center for more information.

Main

Type	S
------	---

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Control Units	Selector switch 3 positions (HAND-OFF-AUTO)
Pilot Light	Green indicator: off type: incandescent with push-to-test
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs
Height	14.13 in (359 mm)
Depth	9.72 in (247 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	UL listed CSA

Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	24.48
Returnability	N

Country of origin	MX
-------------------	----

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
