

Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 3 pole, NEMA 1, 480-120V 60Hz

8903SMG11V81CF4R6TX30

Price*: 2,384.00 USD

! Discontinued

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	3P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Without pilot light
Auxiliary Contacts	3 NO
Control Circuit Fusing	2 fuses primary circuit
Other Options	2P relay (1 NO + 1 NC)
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	7.56 in (192 mm)
Width	14.88 in (378 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications