

Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 3 pole, NEMA 1, 208-120V 60Hz

8903SMG11V84CF4P1T

Discontinued

Main

Type	S
------	---

Complementary

Control Circuit Voltage	208 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Current Rating	30 A
Number Of Poles	3P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	7.56 in (192 mm)
Width	14.88 in (378 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21324-8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	30.22 lb(US) (13.708 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------