

Product data sheet

Characteristics

8903SMG12V01R6

lighting contactor, mechanically held, 30 A, 4 pole, NEMA 1, 24V 60Hz



Price* : 1,551.00 USD



8903SMG12V01R6 has not been replaced. Please contact your customer care center for more information.

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	24 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	4P
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Lugs

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21324 - 8903 S (NOT S°C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	25.390000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
