

# Product data sheet

Specifications

SQUARE D



lighting contactor, mechanically held, 30 A, 4 pole, NEMA 1, 24V 60Hz

8903SMG12V01R6

Price\*: 1,551.00 USD

! Discontinued

## Main

Product	Mechanically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	24 V AC 60 Hz
Current Rating	30 A
Number Of Poles	4P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	2P relay (1 NO + 1 NC)
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	7.56 in (192 mm)
Width	14.88 in (378 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

## Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	25.39 lb(US) (11.517 kg)

## Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months