

8903SMG12V02CFR6

lighting contactor, mechanically held, 30 A, 4 pole,
NEMA 1, 120/110V 60/50Hz



Price** : 2,199.00 USD



8903SMG12V02CFR6 has not been replaced. Please contact your customer care center for more information.

Main

| | |
|---------|--------------------------------------|
| Product | Mechanically Held Lighting Contactor |
| Type | S |

Complementary

| | |
|-------------------------|----------------------------------|
| Control Circuit Voltage | 110 V AC 50 Hz 120 V AC 60 Hz |
| Line Rated Current | 30 A |
| Number of Poles | 4P |
| Control Units | Selector switch (HAND-OFF-AUTO) |
| Pilot Light | No indicator |
| Auxiliary Contacts | Without |
| Control Circuit Fusing | 1 fuse |
| Other Options | 2P relay (1 NO + 1 NC) |
| Electrical connection | Lugs |

Environment

| | |
|------------------------|---|
| Enclosure Type | NEMA 1 painted sheet steel surface and none |
| Product certifications | CSA UL listed |

Ordering and shipping details

| | |
|-----------------------|--------------------------------|
| Category | 21324 - 8903 S (NOT S*C) MECH. |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 25.850000000000001 |
| Returnability | N |
| Country of origin | MX |

Offer Sustainability

| | |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant on 3Q2014 Will be compliant on 3Q2014 |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
