


# 8903SMG12V02X10

lighting contactor, mechanically held, 30 A, 4 pole,  
NEMA 1, 120/110V 60/50Hz



Price\* : 981.00 USD



8903SMG12V02X10 has not been replaced. Please contact your customer care center for more information.

## Main

Product	Mechanically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	4P
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	1 NO
Other Options	None
Electrical connection	Lugs

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

## Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	6
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

Contractual warranty

Warranty period	18 months
-----------------	-----------