

Product data sheet


Characteristics

8903SMG12V04R6

lighting contactor, mechanically held, 30 A, 4 pole, NEMA 1, 277V 60Hz



Price* : 1,551.00 USD



8903SMG12V04R6 has not been replaced. Please contact your customer care center for more information.

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	277 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	4P
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Lugs

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21324 - 8903 S (NOT S°C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	25.390000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 2Q2015 Will be compliant on 2Q2015
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------