

Product data sheet

Characteristics

8903SMG12V81CFF4NP1R6T

lighting contactor, mechanically held, 30 A, 4 pole, NEMA 1, 480-120V 60Hz

Price* : 3,032.00 USD



⚠ Discontinued

8903SMG12V81CFF4NP1R6T has not been replaced.
Please contact your customer care center for more information.

Main

Product	Mechanically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Line Rated Current	30 A
Number of Poles	4P
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	Without
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	Solid neutral terminal block 2P relay (1 NO + 1 NC)
Electrical connection	Lugs
Height	14.13 in (359 mm)
Depth	7.56 in (192 mm)
Width	14.88 in (378 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	32.619999999999997
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------
