

# Product data sheet

Specifications



lighting contactor, electrically held,  
30 A, 2 pole, NEMA 1, 208V 60Hz

8903SMG1V08

⚠ Discontinued on: Dec 12, 2019

⚠ End-of-service on: Oct 15, 2021

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

|         |                                      |
|---------|--------------------------------------|
| Product | Electrically Held Lighting Contactor |
| Type    | S                                    |

## Complementary

|                         |                     |
|-------------------------|---------------------|
| Control Circuit Voltage | 208 V AC 60 Hz      |
| Current Rating          | 30 A                |
| Number Of Poles         | 2P                  |
| Control Units           | No control units    |
| Pilot Light             | Without pilot light |
| Auxiliary Contacts      | Without             |
| Other Options           | None                |
| Electrical Connection   | Lugs                |
| Height                  | 10.00 in (254 mm)   |
| Depth                   | 5.28 in (134 mm)    |
| Width                   | 5.98 in (152 mm)    |

## Environment

|                        |   |
|------------------------|---|
| Enclosure Type         | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed<br>CSA                        |

## Ordering and shipping details

|                   |                                 |
|-------------------|---------------------------------|
| Category          | 21325 - 8903 S (NOT S*C) ELECT. |
| Discount Schedule | CP1                             |
| Returnability     | No                              |
| Country Of Origin | MX                              |

## Packing Units

|                              |                    |
|------------------------------|--------------------|
| Unit Type Of Package 1       | PCE                |
| Number Of Units In Package 1 | 1                  |
| Package 1 Height             | 10.00 in (25.4 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |                         |
|------------------|-------------------------|
| Package 1 Width  | 5.98 in (15.2 cm)       |
| Package 1 Length | 5.28 in (13.4 cm)       |
| Package 1 Weight | 10.50 lb(US) (4.763 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

|                       |  |
|-----------------------|--|
| Eu Rohs Directive     | Not compliant  |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information. |