

Product data sheet

Characteristics

8903SMG2V02CFP21X11

lighting contactor, electrically held, 30 A, 3 pole,
NEMA 1, 120/110V 60/50Hz

Price* : 1,479.00 USD



⚠ Discontinued

8903SMG2V02CFP21X11 has not been replaced.
Please contact your customer care center for more information.

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent with push-to-test
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	1 fuse
Other Options	None
Electrical connection	Lugs
Height	10 in (254 mm)
Depth	134 mm
Width	5.98 in (152 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	24.68
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------
