

Product data sheet

Characteristics

8903SMG2V02Y1006

lighting contactor, electrically held, 30 A, 3 pole,
NEMA 1, 120/110V 60/50Hz



Price* : 3,284.00 USD



8903SMG2V02Y1006 has not been replaced. Please contact your customer care center for more information.

Main

Type	S
------	---

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	23.620000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
-------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
