

# Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,  
30 A, 3 pole, NEMA 1, 480-120V  
60Hz

8903SMG2V81CFF4P1T

Price\*: 1,886.00 USD

! Discontinued

## Main

|         |                                      |
|---------|--------------------------------------|
| Product | Electrically Held Lighting Contactor |
| Type    | S                                    |

## Complementary

|                         |                                                                    |
|-------------------------|--------------------------------------------------------------------|
| Control Circuit Voltage | 480 V AC 60 Hz primary circuit<br>120 V AC 60 Hz secondary circuit |
| Current Rating          | 30 A                                                               |
| Number Of Poles         | 3P                                                                 |
| Control Units           | Selector switch 3 positions HAND-OFF-AUTO)                         |
| Pilot Light             | Red indicator on incandescent                                      |
| Auxiliary Contacts      | Without                                                            |
| Control Circuit Fusing  | 2 fuses primary circuit<br>1 fuse secondary circuit                |
| Other Options           | None                                                               |
| Electrical Connection   | Lugs                                                               |
| Height                  | 15.87 in (403 mm)                                                  |
| Depth                   | 5.20 in (132 mm)                                                   |
| Width                   | 6.34 in (161 mm)                                                   |

## Environment

|                        |                                         |
|------------------------|-----------------------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel surface none |
| Product Certifications | UL Listed<br>CSA                        |

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 30.35 lb(US) (13.767 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|