


8903SMG3V02CG101P1

lighting contactor, electrically held, 30 A, 4 pole,
NEMA 1, 120/110V 60/50Hz



Price** : 1,701.00 USD



8903SMG3V02CG101P1 has not been replaced. Please contact your customer care center for more information.

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	4P
Control Units	Selector switch (HAND-OFF-AUTO)
Pilot Light	Red indicator: on type: incandescent
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and photoelectric receptacle with cell
Product certifications	CSA UL listed

Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	18
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
