

Product data sheet

Specifications

SQUARE D



lighting contactor, electrically held,
30 A, 5 pole, NEMA 1, 120/110V
60/50Hz

8903SMG4V02CP2

Price*: 1,502.00 USD

! Discontinued

Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number Of Poles	5P
Control Units	Selector switch 3 positions HAND-OFF-AUTO)
Pilot Light	Green indicator off incandescent
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	14.13 in (359 mm)
Depth	9.72 in (247 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface none
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	24.48 lb(US) (11.104 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------