

Product data sheet

Characteristics

8903SMG4V03

lighting contactor, electrically held, 30 A, 5 pole,
NEMA 1, 240/220V 60/50Hz

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 831.00 USD



Main

Product	Electrically Held Lighting Contactor
Type	S

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	5P
Control Units	No control units
Pilot Light	No indicator
Auxiliary Contacts	Without
Other Options	None
Electrical connection	Lugs

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	10.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
	Will be compliant on 3Q2014

Contractual warranty

Warranty period	18 months
-----------------	-----------
