


8903SMG70V02C

combo lighting, mechanically held, 3P, 30A, no fuse, NEMA 1, 120/110V 60/50Hz



Price* : 1,794.00 USD



8903SMG70V02C has not been replaced. Please contact your customer care center for more information.

Main

Type	S
------	---

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Line Rated Current	30 A
Number of Poles	3P
Control Units	Selector switch 3 positions (HAND-OFF-AUTO)
Auxiliary Contacts	Without
Other Options	None
Disconnecter device type	Non-fusible disconnect switch
Electrical connection	Lugs
Height	22.99 in (584 mm)
Depth	8.35 in (212 mm)
Width	349 mm

Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	UL listed file E16151 CCN NRNT

Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	28.18
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
