

# Product data sheet

## Characteristics

# 8903SMG70V81A3F4TX11

combo lighting, mechanically held, 3P, 30A, no fuse, NEMA 1, 480-120V 60Hz

Price\* : 2,493.00 USD



⚠ Discontinued

8903SMG70V81A3F4TX11 has not been replaced.  
Please contact your customer care center for more information.

### Main

Type	S
------	---

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Line Rated Current	30 A
Number of Poles	3P
Control Units	Push-button (ON-OFF)
Pilot Light	Without pilot light
Auxiliary Contacts	1 NO + 1 NC
Control Circuit Fusing	2 fuses primary circuit
Other Options	None
Disconnecter device type	Non-fusible disconnect switch
Electrical connection	Lugs
Height	22.99 in (584 mm)
Depth	8.35 in (212 mm)
Width	349 mm

### Environment

Enclosure Type	NEMA 1 painted sheet steel surface and none
Product certifications	UL listed file E16151 CCN NRNT

### Ordering and shipping details

Category	21324 - 8903 S (NOT S*C) MECH.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	32.369999999999997
Returnability	N

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---